

PRELIMINARY

# MATERIAL LIST

FINAL

TOTAL SHEETS 5

FOR

REVISION

TMC MODEL - BMA429-2

TITLE - CHAS ASSY SVO

| REV. | SHEET (S)     | DATE    | APPR. |
|------|---------------|---------|-------|
| X3   |               |         | BN    |
| Ø    |               | 4/12/72 |       |
| A    | 3             | 5/22/72 | EJ    |
| B    | 4, Added Sh 5 | 8/10/72 | EJ    |
|      |               |         |       |
|      |               |         |       |
|      |               |         |       |
|      |               |         |       |

USED ON  
MODEL -  
AX5113-2

CONSISTS OF  
SUPPORTING LISTS

NONE

LAST SYMBOLS    SYMBOLS NOT USED

COMPILED B.N.  
CHECKED \_\_\_\_\_  
ENG APPR [Signature]  
FNL APPR [Signature]  
ISS DATE \_\_\_\_\_

NOTE: REFER TO AX5113-2 FOR LAST SYMBOLS AND SYMBOLS NOT USED.

ENGINEERING JOB NUMBER  
# E \_\_\_\_\_

§ FOR SPECIAL NOTES,  
REFER TO S1200.

# MATERIAL LIST

BMA429-2  
REV. *B*

PAGE 1 OF

| PART NUMBER  | DESCRIPTION      | USED ON  | QTY. | QTY. PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S1200 |
|--------------|------------------|----------|------|---------------|-------------------|------------------------------|
| CA1506       | WRG HARN, BRCH   | BMA429-2 | 1    | 1*            | W1001             |                              |
| CC100-28     | CAP, FXD, CER    | BMA429-2 | 1    |               | C1103             |                              |
|              |                  | BMA429-2 | 1    | 2*            | C1113             |                              |
| CC109-6      | CAP., FXD CER    | BMA429-2 | 1    | 1*            | C1001             |                              |
| CE51C800R    | CAP., FXD, ELEC  | BMA429-2 | 1    |               | C1104             |                              |
|              |                  | BMA429-2 | 1    | 2*            | C1105             |                              |
| CE116-10VN   | CAP., FXD, ELEC  | BMA429-2 | 1    |               | C1101             |                              |
|              |                  | BMA429-2 | 1    | 2*            | C1102             |                              |
| CI101-5Q2    | CORE, U          | TR192    | 6    | 6*            |                   |                              |
| CL138        | COIL, RF         | BMA429-2 | 1    | 1*            | L1405             |                              |
| CP41B1EF405K | CAP., FXD, PAPER | BMA429-2 | 1    | 1*            | C1106             |                              |
| CU102-2      | CLAMP, LOOP      | BMA429-2 | 3    | 3*            |                   |                              |
| CU102-5      | CLAMP, LOOP      | BMA429-2 | 1    | 1*            |                   |                              |
| CU102-7      | CLAMP, LOOP      | BMA429-2 | 2    | 2*            |                   |                              |
| CU102-9      | CLAMP, LOOP      | BMA429-2 | 1    | 1*            |                   |                              |
| CU102-13     | CLAMP, LOOP      | BMA429-2 | 1    | 1*            |                   |                              |
| CU118-4S     | CLAMP, TUBE      | BMA429-2 | 2    | 2*            |                   |                              |
| DD124        | RECT, SCOND DEV  | BMA429-2 | 1    | 1*            | CR1106            |                              |
| DD146-2      | RECT, SCOND DEV  | BMA429-2 | 1    | 1*            | CR1103            |                              |
| EY107-2      | GROM, NYLON      | BMA429-2 |      |               |                   |                              |

# MATERIAL LIST

BMA429-2  
REV. B

PAGE 2 OF

| PART NUMBER   | DESCRIPTION     | USED ON       | QTY. | QTY. PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S1200 |
|---------------|-----------------|---------------|------|---------------|-------------------|------------------------------|
| EY102-13      | GROM, RUB       | BMA429-2      | 1    | 1*            |                   |                              |
| EY102-15      | GROM, RUB       | BMA429-2      | 1    | 1*            |                   |                              |
| GL 143        | ADHESIVE        | TR192         |      |               |                   |                              |
| GL125         | ADH, EPOXY      | TR192         |      |               |                   |                              |
| IM226-2M      | INS, SCOND      | BMA429-2      | 3    | 3*            |                   |                              |
| LD2374/MS5562 | PL, REAR        | BMA429-2      | 1    | 1*            |                   |                              |
| LD2397/MS5548 | BRKT, MTG, CONN | BMA429-2      | 1    | 1*            |                   |                              |
| LD2404/MS5604 | SUB-CHAS, SVO   | BMA429-2      | 1    | 1*            |                   |                              |
| MS5140        | BRKT, MTG, XFMR | TR192         | 1    | 1*            |                   |                              |
| MS5548        | BRKT, MTG, CONN | LD2397/MS5548 | 1    | 1*            |                   |                              |
| MS5561        | PL, SD, RT      | BMA429-2      | 1    | 1*            |                   |                              |
| MS5562        | PL, REAR        | LD2374/MS5562 | 1    | 1*            |                   |                              |
| MS5604        | SUB-CHAS, SVO   | LD2404/MS5604 | 1    | 1*            |                   |                              |
| MS3102A18-16P | CONN, RECP, ML  | BMA429-2      | 1    | 1*            | J1004             |                              |
| PM1019-2      | SPT, SLIDE, SVO | BMA429-2      | 1    | 1*            |                   |                              |
| PM1020-2      | SPT, SLIDE, SVO | BMA429-2      | 2    | 2*            |                   |                              |
| PM1204-2      | GUIDE           | BMA429-2      | 2    | 2*            |                   |                              |
| PM1332        | BUTTON, CONT    | BMA429-2      | 1    | 1*            | E1001             |                              |

# MATERIAL LIST

BMA429-2  
REV. *B*

PAGE 3 OF

| PART NUMBER     | DESCRIPTION      | USED ON  | QTY. | QTY. PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S1200 |
|-----------------|------------------|----------|------|---------------|-------------------|------------------------------|
| PX1007          | CAP., CONT, HLDR | BMA429-2 | 1    | 1*            |                   |                              |
| PX1153          | SPACER, COIL     | TR192    | 4    | 4*            |                   |                              |
| RC20GF102J      | RES, FXD, COMP   | BMA429-2 | 1    | 1*            | R1109             |                              |
| RC20GF272J      | RES, FXD, COMP   | BMA429-2 | 1    | 1*            | R1103             |                              |
| RC42GF181J      | RES, FXD, COMP   | BMA429-2 | 1    | 1*            | R1102             |                              |
| RC42GF474J      | RES, FXD, COMP   | BMA429-2 | 1    |               | R1104             |                              |
|                 |                  | BMA429-2 | 1    | 2*            | R1108             |                              |
| RL168-3C10-24DC | REL, ARM., 3PDT  | BMA429-2 | 1    | 1*            | K1101             |                              |
| RW109-2         | RES, FXD, WW 10W | BMA429-2 | 1    | 1*            | R1101             |                              |
| RW109-9         | RES, FXD, WW 10W | BMA429-2 | 1    | 1*            | R1107             |                              |
| RW109-14        | RES, FXD, WW 10W | BMA429-2 | 1    | 1*            | R1106             |                              |
| RW109-24        | RES, FXD, WW 10W | BMA429-2 | 1    | 1*            | R1105             |                              |
| TE0102-2        | TERM., STUD, INS | BMA429-2 | 1    |               | E1101             |                              |
|                 |                  | BMA429-2 | 1    |               | E1102             |                              |
|                 |                  | BMA429-2 | 1    |               | E1103             |                              |
|                 |                  | BMA429-2 | 1    |               | E1104             |                              |
|                 |                  | BMA429-2 | 1    |               | E1105             |                              |
|                 |                  | BMA429-2 | 1    | 6*            | E1106             |                              |
| TE0104-2        | TERM., LUG, LKG  | BMA429-2 | 1    | 1*            |                   |                              |
| TE0104-3        | TERM., LUG, LKG  | BMA429-2 | 1    | 1*            |                   |                              |
| TE0110-1        | TERM., LUG       | BMA429-2 | 1    | 1*            |                   |                              |

# MATERIAL LIST

BMA429-2  
REV. *B*

PAGE 4 OF

| PART NUMBER | DESCRIPTION      | USED ON  | QTY. | QTY. PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S1200 |
|-------------|------------------|----------|------|---------------|-------------------|------------------------------|
| TE0149-120  | TERM., LUG       | BMA429-2 | 7    | 7*            |                   |                              |
| TE0149-144  | TERM., LUG       | BMA429-2 | 4    | 4*            |                   |                              |
| TE0154-130  | TERM., LUG       | BMA429-2 | 1    | 1*            |                   |                              |
| TF375       | XFMR, PWR        | BMA429-2 | 1    | 1*            | T1101             |                              |
| TF5028      | COIL, CHOKE      | BMA429-2 | 1    | 1*            | L1101             |                              |
| TR192       | XFMR, OUT. MATCH | BMA429-2 | 1    | 1*            | L1001             |                              |
| TS100-6     | SOC, EL TUBE     | BMA429-2 | 1    | 1*            | XF1101            |                              |
| TS166-1     | SOC, SCOND DEV   | BMA429-2 | 1    |               | XCR1107           |                              |
|             |                  | BMA429-2 | 1    |               | XCR1108           |                              |
|             |                  | BMA429-2 | 1    | 3*            | XCR1109           |                              |
| UG492*/U    | ADAPT, CONN, RF  | BMA429-2 | 1    |               | J1005             |                              |
|             |                  | BMA429-2 | 1    | 2*            | J1006             |                              |
| UG560*/U    | CONN, RECP, RF   | BMA429-2 | 1    | 1*            | J1007             |                              |
| WA102-4     | WASH, FBR, SHLDR | BMA429-2 | 8    | 8*            |                   |                              |
| WI139-1     | WIRE, ELEC, TEF  | TR192    |      |               |                   |                              |
| 1N547       | SCOND, DEV, DIO  | BMA429-2 | 1    | 1*            | CR1101            |                              |
| 1N2841R     | SCOND, DEV, DIO  | BMA429-2 | 1    |               | CR1107            |                              |
|             |                  | BMA429-2 | 1    |               | CR1108            |                              |
|             |                  | BMA429-2 | 1    | 3*            | CR1109            |                              |
| 1N2976B     | SCOND, DEV, DIO  | BMA429-2 | 1    | 1*            | CR1105            |                              |
| 1N3321B     | SCOND, DEV, DIO  | BMA429-2 | 1    | 1*            | CR1104            |                              |

# MATERIAL LIST

BMA429-2  
REV. *b*

PAGE 5 OF

| PART NUMBER   | DESCRIPTION  | USED ON              | QTY.   | QTY. PER UNIT | REFERENCE SYMBOLS | SPECIAL NOTES REFER TO S1200 |
|---------------|--------------|----------------------|--------|---------------|-------------------|------------------------------|
| TS100-3       | SOC, EL TUBE | BMA429-2<br>BMA429-2 | 1<br>1 | 2*            | XC1104<br>XC1105  |                              |
| BS            | SOLDER SOFT  | TR192                |        |               |                   |                              |
| 5/22/72 REV A | EMN 20701    |                      |        |               |                   |                              |
| 8/10/72 REV B | EMN 20817    |                      |        |               |                   |                              |