

MATERIAL LIST

REV.

MODEL BSP-1C

SHEET 1 OF 6

| QUAN. PER UNIT | PART NO. | DESCRIPTION SUPPORTING LISTS | REF. | ITEM LOCATION | | | REF. SYMBOLS AND/OR REMARKS |
|-------------------|-------------|---------------------------------|------|---------------|------------------|-------|--------------------------------|
| | | | | USED ON | USED TO MOUNT | QUAN. | |
| | NPL-AZ-104A | Amplifier, Audio Frequency | | | | | |

| MATERIAL LIST | | REV. | | | | | | | | | | | MODEL | BSP-1 C | | |
|-------------------|---------------|--------------------------------------|---------|---------------|------------------|-------|--------------------------------|--|--|--|--|--|-------|---------|----|---|
| | | | | | | | | | | | | | SHEET | 2 | OF | 6 |
| QUAN. PER UNIT | PART NO. | DESCRIPTION ELECTRICAL/MECHANICAL | REF. | ITEM LOCATION | | | REF. SYMBOLS AND/OR REMARKS | | | | | | | | | |
| | | | | USED ON | USED TO MOUNT | QUAN. | | | | | | | | | | |
| 1 | AZ-104A | Amplifier, Audio Frequency | | A-2588-4 | | 1 | AR101 | | | | | | | | | |
| 4 | CU-139-2B | Ferrule, Handle | | A-2588-4 | | 4 | | | | | | | | | | |
| 1 | FH-104-2 | Holder, Fuse | | A-2588-4 | | 1 | XF101(DS101,R102) | | | | | | | | | |
| 1 | FU-100-.250 | Fuse, Cartridge, 1/4 Amp. | 115 VAC | A-2588-4 | | 1 | F101 | | | | | | | | | |
| 1 | FU-100-.125 | FUse, Cartridge 1/8 Amp. | 230 VAC | A-2588-4 | | 1 | F101 | | | | | | | | | |
| 2 | HA-102-2BN | Handle | | A-2588-4 | | 2 | | | | | | | | | | |
| 1 | LD1172/MS3064 | Panel, Front | | A-2588-4 | | 1 | | | | | | | | | | |
| 1 | LS-101 | Speaker, P.M. | | A-2588-4 | | 1 | LS101 | | | | | | | | | |
| 1 | MP-100-1 | Knob, Instrument, Fluted Type | | A-2588-4 | | 1 | | | | | | | | | | |
| 1 | MS-395 | Grill, Speaker | | A-2588-4 | | 1 | | | | | | | | | | |
| 1 | MS-3064 | Panel, Front | Mach | LD-1172 | | 1 | | | | | | | | | | |
| 1 | NP-103-76 | Nameplate, Identification | Comm. | A-2588-4 | | 1 | When Required | | | | | | | | | |
| 1 | NP- | Nameplate, Identification | Navy | A-2588-4 | | 1 | When Required | | | | | | | | | |
| 1 | NP645 | Plate, Adapter, Fuse | 230 VAC | A-2588-4 | | 1 | When Required | | | | | | | | | |
| 1 | PL-218 | Connector, Plug, AC, 3/C | | CA-575-5 | | 1 | P101 | | | | | | | | | |
| 1 | NP-764 | Plate, Adapter, Fuse | 115 VAC | A-2588-4 | | 1 | When Required | | | | | | | | | |
| 1 | RV4NAYS253A | Resistor, Variable, Composition | | A-2588-4 | | 1 | R101 | | | | | | | | | |

| MATERIAL LIST | | REV. | | | | | | | | | | | MODEL | BSP-1 C | | |
|-------------------|--------------|--------------------------------|------|---------------|------------------|-------|--------------------------------|--|--|--|--|--|-------|---------|----|---|
| | | | | | | | | | | | | | SHEET | 3 | OF | 6 |
| QUAN. PER UNIT | PART NO. | DESCRIPTION HARDWARE | REF. | ITEM LOCATION | | | REF. SYMBOLS AND/OR REMARKS | | | | | | | | | |
| | | | | USED ON | USED TO MOUNT | QUAN. | | | | | | | | | | |
| 4 | LWS10MRN | Washer, Lock, Split | | A-2588 -4 | | 4 | | | | | | | | | | |
| 4 | SCBP0832BN10 | Screw, Machine | | A-2588 -4 | | 4 | | | | | | | | | | |
| 4 | SCHH1032BN8 | Screw, Machine | | A-2588 -4 | | 4 | | | | | | | | | | |
| 4 | SFB0256SN3 | Screw, Tapping, Thread Cutting | | A-2588 -4 | | 4 | | | | | | | | | | |
| 10 | TE-120-2 | Lug, Solderless | | CA-575-5 | | 3 | | | | | | | | | | |
| | | | | CA-676-3 | | 2 | | | | | | | | | | |
| | | | | CA-676-4 | | 2 | | | | | | | | | | |
| | | | | CA-676-5 | | 3 | | | | | | | | | | |

MATERIAL LIST

REV.

MODEL BSP-1G

SHEET 4 OF 6

| QUAN. PER UNIT | PART NO. | DESCRIPTION RAW MATERIALS | REF. | ITEM LOCATION | | | REF. SYMBOLS AND/OR REMARKS |
|-------------------|---------------|------------------------------|-------|---------------|------------------|-------|--------------------------------|
| | | | | USED ON | USED TO MOUNT | QUAN. | |
| | BS-10Q | Solder, Soft | | | | | |
| 0-9 | MWC18(16)U0 | Wire, Electrical | Black | CA-676-4 | | 0-9 | |
| 0-9 | MWC18(16)U2 | Wire, Electrical | Red | CA-676-4 | | 0-9 | |
| 0-7 | MWC22(7)U0 | Wire, Electrical | Black | CA-676-3 | | 0-7 | |
| 0-7 | MWC22(7)U2 | Wire, Electrical | Red | CA-676-3 | | 0-7 | |
| 0-5 | PX-100-1- 133 | Sleeving, Size 8 | Black | CA-676-3 | | 0-5 | |
| 0-7 | PX-100-1- 148 | Sleeving, Size 7 | Black | CA-676-4 | | 0-7 | |
| 1 | WI-134-6-12 | Cable, Power, Coiled | | CA-575-5 | | 1 | |
| 0-9 | WI-142-2 | Cable, Special Purpose | | CA-676-5 | | 0-9 | |

| MATERIAL LIST | | REV. | | | | | | | | | | | MODEL | BSP-1C | | |
|-------------------|---------------|------------------------------------|------|---------------|------------------|-------|--------------------------------|--|--|--|--|--|-------|--------|----|---|
| | | | | | | | | | | | | | SHEET | 5 | OF | 6 |
| QUAN. PER UNIT | PART NO. | DESCRIPTION SUPPORTING DRAWINGS | REF. | ITEM LOCATION | | | REF. SYMBOLS AND/OR REMARKS | | | | | | | | | |
| | | | | USED ON | USED TO MOUNT | QUAN. | | | | | | | | | | |
| 1 | A-2588-4 | Final Assembly, BSP-1C | | BSP-1 C | | | | | | | | | | | | |
| 1 | CA-575-5 | Cable Assembly, -Power, DC | | A-2588 -4 | | 1 | W101 | | | | | | | | | |
| 1 | CA-676-3-7.00 | Cable Assembly, Ampl. to Speaker | | A-2588 -4 | | 1 | | | | | | | | | | |
| 1 | CA-676-4-9.00 | Cable Assembly, Ampl. to Fuse | | A-2588 -4 | | 1 | | | | | | | | | | |
| 1 | CA-676-5-9.00 | Cable Assembly, Potentiometer | | A-2588 -4 | | 1 | | | | | | | | | | |
| 1 | CK-613 | Schematic Diagram | | BSP-1C | | | | | | | | | | | | |

| MATERIAL LIST | | REV. | | | | | | | | | | | MODEL | BSP-1C | | |
|-------------------|----------|-------------------------------|------|-------------------|------------------|-------|--------------------------------|--|--|--|--|--|-------|--------|----|---|
| | | | | | | | | | | | | | SHEET | 6 | OF | 6 |
| QUAN. PER UNIT | PART NO. | DESCRIPTION SPECIFICATIONS | REF. | ITEM LOCATION | | | REF. SYMBOLS AND/OR REMARKS | | | | | | | | | |
| | | | | USED ON | USED TO MOUNT | QUAN. | | | | | | | | | | |
| | S-114 | Zinc Chromate Primer | | MS-3064 | | | | | | | | | | | | |
| | S-115 | Smooth Gray Enamel | | MS-3064 | | | | | | | | | | | | |
| | S-404 | Yellow Iridite | | MS-3064 MS-395 | | | | | | | | | | | | |
| | S-833 | Test Procedure | | BSP-1C | | | | | | | | | | | | |